

**All INCAL DVD-ROMs are available for download at <https://www.cummins.com/support/digital-products-and-services-support/incal-support>**

Enclosed are the April 2025 INCAL DVD-ROMs.

Please take a moment to review the information in this cover letter for details regarding the contents of the INCAL DVD-ROMs.

### Changes in Calibrations

New engine control module (ECM) calibration codes have been released using industry standard encryption for all electronically controlled engine products. These ECM calibration codes are only supported in Cummins INSITE™ electronic service tool version 8.8.0 and newer. If users do not upgrade, users will not be able to use any calibrations on these INCAL DVDs, downloaded through QuickServe Online (QSOL), or INSITE ECM/PDD Code Search. INSITE 8.8.0 is compatible with any INCAL DVDs created after March 2022.

### What is INCAL?

The first DVD contains calibrations for Automotive applications, Programmable Datalink devices, and additional files. The second, third, fourth, fifth, sixth, seventh and eighth DVDs contains calibrations for Automotive applications. The ninth, tenth, eleventh and part of the twelfth DVDs contains calibrations for Industrial applications. The twelfth DVD also contains calibrations for HHP/Power Gen applications. For the INCAL DVD details, please see the listings below.

### Additional Files:

Cummins ED-4 Display- used for the Marine C Command Connect and Connect Premier Panel System

### April 2025 INCAL DVD-ROMs Content:

#### DVD 1 – Automotive Engines

6.7N CM2380 D109B	B4.5 CM2620 B158B	ISB	ISB4.5/6.7 ISD4.5/6.7 CM2150 SN (Euro 4.5)
A10 CM2670 L157B	B5.6 CM2670 B187B	ISB - CM2150	ISB4.5/6.7 ISD4.5/6.7 CM2150 SN (Euro 5)
A7 CM2670 B205B	B5.9G	ISB Daimler Chrysler	ISB5.9G/ISC8.3G CM2180/CM2380 C101
A8.5 CM2670 L153B	B6.2 CM2670 B156B	ISB/ISD4.5 CM2150 B119 ISB/ISD6.7 CM2150 B120	ISB6.7 G CM2180/CM2380 B118
Agility® Fuel Delivery System CM1881 AFS101	B6.2 CM2670 B202B	ISB/ISD6.7 CM2880 B126	ISBe (4 and 6 Cylinder)
B4.0 CM2620 B154B	B6.7 CM2350 B121B/B141B/B179B	ISB3.9 CM2220 B107	ISBe2/3 - CM850
B4.5 CM2220 B186B	B6.7 CM2450 B181B	ISB4.5 CM2350 B104	ISBe4 (4 and 6 cylinder)
B4.5 CM2220 B190B	C Gas/B Gas Plus	ISB4.5 CM2620 E	ISC/ISL
B4.5 CM2350/CM2450 B129B/B147B/B214B/B215B	C8.3G	ISB4.5/6.7 ISD4.5/6.7 CM2150 SN	

DVD 1 – PDD

Aftertreatment Diesel Exhaust Fluid Controller	Electric Fuel Lift Pump	Fuel Control Valve	Throttle Actuator
Aftertreatment Diesel Exhaust Fluid Dosing Unit	Engine Fuel Supply Pump	Ignition Control Module	Turbo Actuator Controller

DVD 1 – Additional Files

DVD 2 – Automotive Engines

B6.7 CM2350/CM2450 B135B/B148B/B216B/B217B	B6.7 CM2670 B182B	ISB5.6 CM2670 B152B	ISB5.9 CM2880 B149
B6.7 CM2450 B155B	B6.7 CM2670 B188B	ISB5.9 CM2150 B111	ISB5.9 CM2880 B172
B6.7 CM2670 B153B	B6.7N CM2380 B150B	ISB5.9 CM2880	ISB-CM850
B6.7 CM2670 B163B	B6.7N CM2380 B183B	ISB5.9 CM2880 B110	
B6.7 CM2670 B167B/B168B/B169B	BES CM2450 EV105B/EV107B/EV110B	ISB5.9 CM2880 B127	
B6.7 CM2670 B173B	BES CM2450 EV109B	ISB5.9 CM2880 B140	

DVD 3 – Automotive Engines

D4.0 CM2620 D103B	F4.5 CM2620 F146B	ISD4.5 NSV/ISB5.9 NS4/ISDe6.7 NS4 CM2880 WFLD	ISF2.8 CM2220 F122
D4.5 CM2620 D104B	F4.5 CM2620 F166C	ISD5 CM2620 EUVI	ISF2.8 CM2220 F126
D6.7 CM2670 D102B/D106B/D107B	ISB6.2 CM2670 E	ISD6.7 CM2880 D101	ISF2.8 CM2220 IAN
D7.0 CM2670 B203B	ISB6.7 CM2250	ISD6.7 CM2880 D101	ISF2.8/3.8 CM2220
F2.5 CM2620 F150B	ISB6.7 CM2350 B101	ISDE CM2150	ISF2.8/3.8 CM2220 AN
F2.8 CM2620 F135B	ISB6.7 CM2350 B103/B142	ISF2.8 CM2220 AN	ISF2.8/3.8 CM2220 IAN/F122
F2.8 CM2620 F136B	ISB6.7 ISD6.7 CM2150	ISF2.8 CM2220 EC/ECF2/ECCF2	
F3.8 CM2350 F132B	ISC - CM2150	ISF2.8 CM2220 F101	B6.7 G CMOH6.0 B125
<b>F3.8 CM2450 F156C</b>	ISC/Transit Bus ISL8.3 - CM850	ISF2.8 CM2220 F117	ISG12 G CMOH6.0 G111
F3.8 CM2450 F157C	ISC8.3 CM2250	ISF2.8 CM2220 F121	L8.9G CMOH2.0 L125B

DVD 4 – Automotive Engines

F3.8 CM2620 F137B/F138B	ISF3.8 CM2620 A	ISL9 CM2150 SN (Euro 4.5)	L10G
F3.8 CM2620 F144B	ISF3.8/ISD4.5 CM2220 F103/D108/F115	ISL9 CM2250	L9 CM2350 L116B
F4.5 CM2620 F139B/F140B	ISL CM2150	ISL9 CM2350 L101/L123B	L9 CM2350/CM2450 L119B/L169B
ISF2.8/4.5 CM2220 F123/F129	ISL G - CM2180/CM2380	ISL9 CM2350 L111	L9 CM2670 L128B
ISF3.8 CM2220 AN	ISL8.9 - CM850	ISL9.5 CM2150 SN	L9 CM2670 L132B
ISF3.8 CM2220 F110/F116	ISL8.9 CM2150 SN (Euro 5)	ISL9.5 NS5 2880E IAT	L9N CM2380 L124B/L130B/L142B/L147B
ISF3.8 CM2220 F134B	ISL8.9 CM2670 E	ISLe - CM2150	M10 CM2670 L156B
ISF3.8 CM2220 IAN	ISL8.9 CM2880 L112	ISLe4 (6 cylinder)	M10 CM2670 L158B
ISF3.8 CM2350 F109	ISL8.9/ISL9.5 CM2880 L138/L140	ISV5 CM3230 V104	M10 CM2880 L172B/L173B
ISF3.8 CM2350 F120	ISL9 CM2150 SN	L Gas Plus	M8.5 CM2670 L152B

DVD 5 – Automotive Engines

A12/X12 CM2670 X148B	ISM - CM870	ISX - CM871	M12/M13 CM2670 M116B
A13/X13 CM2670 X149B	ISM - CM875	ISX/ISZ13 CM2150 SN	M8.5 CM2670 L154B
Celect	ISM CM876	ISX11.9/12/15 CM2250	R2.8 CM2220 R101B
Celect Plus	ISM11 CM876 M103	ISX12 G CM2180/CM2380 EJ	Z10 CM2670 L159B
ISG11 CM2880 G106/G108 ISG12 CM2880 G107/G109	ISM11 CM876 SN	L9 CM2450 L126B/L127B	Z8.5 CM2670 L155B
ISM	ISM-Fuel Control Module - CM570	M12/M13 CM2670 M115B	

DVD 6 – Automotive Engines

15N CM2380 M104B/M105B	M12/M13 CM2880 M119B/M120B	N14 CM876 N108B	X11 CM2670 X126B
ISX12/15 CM2350 X101/X102	M15 CM2670 M106B	Signature/ISX	X12 CM2450 X137B
ISX12N CM2380 X120B	M15 CM2670 M107B/M108B/M109B	Signature/ISX - CM870	

DVD 7 – Automotive Engines

ISX15 CM2250 SN	X12 CM2670 X136B	X15 CM2350/CM2450 X123B/X154B
X12 CM2350 X119B	X13 CM2670 X122B	X15 CM2350/CM2450 X123B/X155B
X12 CM2670 X121B/X136B	X15 CM2350 X114B/X116B	X15 CM2350/CM2450 X129B/X153B

DVD 8 – Automotive Engines

ISZ13 CM2150 Z105	X15 CM2450 X124B/X134B	X15N CM2380 X150B	Z15 CM2670 Z107B
ISZ13 CM2150 Z106B	X15 CM2450 X142B	Z12/Z13 CM2670 M117B	
ISZ13 NSV 2880E IAT	X15 CM2670 X145B	Z14 CM2670 NSVI	
ISZ14 E5 CM2880H	X15D CM2670 M118B	Z14 CM2670 Z103B	

DVD 9 – Industrial Engines

480C-E	B6.7 CM2350 B136C/B157C	QSB3.3 - CM2150	<b>QSB4.5 CM2450 B226C</b>
B3.9 CM2620 B171C/B211C	B6.7 CM2350 B198C	QSB3.3 CM2250 EC/B137	<b>QSB4.5 CM2670 B201C</b>
B4.5 CM2350 B146C/B159C	B6.7 CM2450 B177C	QSB3.9 CM2880 B138/QSB5.9 CM2880 B139	QSB5.9 CM2880 B115/QSB6.7 CM2880 B116
B4.5 CM2350 B160M/B161M	B6.7/B7 CM2670 B164C/B165C/B213C	QSB4.5 CM2150 B108/QSB6.7 CM2150 B109	QSB5.9/44, 5.9/30, 4.5/30, 3.9/30
<b>B4.5 CM2450 B218M/B219M</b>	F3.8 CM2350 F128C/F143C	QSB4.5 CM2250 EC/B131	QSC8.3/QSL9
B4.5 CM2450 B230C	F3.8 CM2350 F154C	QSB4.5 CM2350 B106/B122/B144	
B5.9 CM2670 B166C/B212C	Komatsu StageV MR 6.7/8.9	QSB4.5 CM2350 B174C	

DVD 10 – Industrial Engines

<b>F3.8 CM2450 F170C</b>	QSB6.7 CM2250 EC/B128	QSB6.7/QSL8.9 CM2350 CSIV	QSC8.3 CM850(CM2850)
F4.5 CM2450 F151C	QSB6.7 CM2350 B105/B130/B145	QSB6.7/QSL8.9 CM2350 T4F	QSF2.8 CM2880 F105/F114/F124/F131
F4.5 CM2620 F141C	QSB6.7 CM2350 B170C/B185C	QSB6.7-M CM2250	QSF2.8/3.8 CM2880 F104/F108/F112

F4.5 CM2620 F152C/F164C	QSB6.7/QSL 9 CM2250	QSB7 CM2880 B117/QSL9.3 CM2880 L113	
QSB4.5/6.7 CM850(CM2850) / QSB5.9 CM850	QSB6.7/QSL 9 CM2250 Komatsu	QSC8.3 CM2880 C102	

### DVD 11 – Industrial Engines

Celect Plus Industrial	F3.8 CM2450 F169C/F171C	L9 CM2450 L166C	QSG12/X12 CM2350 G110/G113/X144C
CENSE	L9 CM2350 L120C/L129C/L133C	L9 CM2670 L134C/L135C/L136C/L137C/L168C	QSL9 CM2250 L106
Centinel	L9 CM2350 L148C	Next Generation Cense CM2330	QSL9 CM2250 L115
CENTRY	L9 CM2350 L151C	PIM	QSL9 CM2350 L102/L118/L122
Centry CM2940	L9 CM2450 L164C/L165C	QSF3.8/F3.8 CM2350 F107/F118/F119/F125/F133C/F142C	QSL9 CM850(CM2850)

### DVD 12 – Industrial Engines

M14 CM2670 M111C/M15 CM2670 M112C	QSX15 CM2250 ECF/X115	VTA903 CM2250 V105	X15 CM2350 X132C
M15 CM2670 M114C	QSX15 CM570 X147G	X12 CM2670 X135C	X15 CM2350 X139C
QSM11	QSZ13 CM2150 Z101	X15 CM2350 X125M/X131	Z13 CM2880 Z104G
QSN14 CM876 N103/N105	QSZ13 CM2150 Z102	X15 CM2350 X127C/QSX15 CM2350 X105/X106/X118	Z14 CM2670 Z109C
QSNT14 CM876 N102	R2.8 CM2220 R102C	X15 CM2350 X130C/X140C	

### DVD 12 – HHP/PowerGen Engines

B3.9/B5.9/B6.7/L8.9 CM2880 B194G/195G/192G/191G/L146G	QSK19 CM2450 K155G	QSK50 CM2350 K163C - Primary	QSK95 CM2350 K113/K128M/K143C/K147C - Primary
B4.5 CM2670 B178G	QSK19 CM850/CM2150/CM2850 MCRS G/K139M	QSK50 CM2350 K163C - Secondary	QSK95 CM2350 K113/K143C/K147C - Secondary
B6.7 CM2670 B175G	QSK19 CM850/CM2150/CM2850 MCRS/K139M	QSK50/60 CM2350 K108/K116/K117/K121/K 130/K133/K135/K136 - Primary	QSK95 CM2350 K143C - Primary
Gas Cense - QSK19G/45G/60G, QSV81/91 - CM850	QSK19/23 CM2350 K105/K114/K115/K127	QSK50/60 CM2350 K108/K116/K121/K133/K 135/K136 - Secondary	QSK95 CM2350 K143C - Secondary
Gas Compression GTA, KTA	QSK19/K19 CM2350 K144G/K164G	QSK50/60 CM850/CM2150/CM2850 MCRS G/K140M - Primary	QSK95 Tier2 Marine CM2350 - Primary
HSK78G CM2358 K129G - Primary	QSK23/60/78 CM500/CM2250 K104/K109/K112/K157G/K 159G/K160G	QSK50/60 CM850/CM2150/CM2850 MCRS G/K140M - Secondary	QSK95 Tier2 Marine CM2350 - Secondary
HSK78G CM2358 K129G - Secondary	QSK38 CM2350 K125/K138M - Primary	QSK50/60 CM850/CM2150/CM2850 MCRS/K132M/K140M - Primary	QSL9 CM2350 L107
M15 CM2670 M113G	QSK38 CM2350 K125/K138M - Secondary	QSK50/60 CM850/CM2150/CM2850 MCRS/K132M/K140M - Secondary	QSL9 CM2670 L145G
QSB4.5/6.7/7-DM CM850(CM2850)	QSK38 CM850/CM2150/CM2850 MCRS G/K106M/K142M - Primary	QSK60 CM2350 K149M - Primary	QSL9 CM850(CM2850)

QSB6.7 CM2350 B112	QSK38 CM850/CM2150/CM2850 MCRS M/K142M - Secondary	QSK60 CM2350 K149M - Secondary	QSM11 CM876 Power Gen/QSM11 CM876 M101/M102M
QSG12 CM2880 G112	QSK38 CM850/CM2150/CM2850 MCRS/K106M/K142M - Primary	QSK78 CM2350 K126/K137/K154C - Primary	QSM15 CM2670 M110G
QSK 19/23/45/60/78	QSK38 CM850/CM2150/CM2850 MCRS/K142M - Secondary	QSK78 CM2350 K126/K137/K154C - Secondary	QST30
QSK 19G/38G/60G, QSV81/91 - CM700/CM2358	QSK38/K38 CM2350 K145G/K165G - Primary	QSK78 CM2450 K161G - Primary	QST30 - Power Gen
QSK 19G/38G/60G, QSV81/91 - SSM558/CM2358	QSK38/K38 CM2350 K145G/K165G - Secondary	QSK78 CM2450 K161G - Secondary	QST30 CM2350 T101/T103C - Primary
QSK 23/60/78 CM500 K157G/ K159G/K160G	QSK50 CM2350 K146G - Primary	QSK95 CM2350 K111 - Primary	QST30 CM2350 T101/T103C - Secondary
QSK 23/60/78 CM500 Power Gen	QSK50 CM2350 K146G - Secondary	QSK95 CM2350 K111 - Secondary	QST30 CM850

\*The engine products in **bold** are new products released on the INCAL DVDs.

### Have Comments?

We would like to know how well this information meets your needs. Please call Cummins Electronic Support Products at 1-800-CUMMINS (select option 2 and then option 3) with your comments.