

INSITE 8.4.1 Features Notes

The latest INSITE information can be found on the website:

<https://www.cummins.com/support/electronic-service-tools-support>

For technical support, please either call 1-800-CUMMINS or send an email to

servicetoolssupport@cummins.com.

To locate the nearest distributor, visit this website:

<https://locator.cummins.com>

Table of Contents

1. General Information	2
1.1 Upgrade Capability	2
1.2 Fault Information System (FIS)	2
2. New Base Features	2
3. New Diagnostic Tests	2
3.1 Aftertreatment Diesel Filter Regeneration Analyzer	2
4. New Advanced ECM Data	2
5. New Features and Parameters	2
6. New Product Support	2
7. Supported Languages	2
8. Supported Operating Systems	3
9. PC Requirements	3
9.1 Recommended	3
9.2 Minimum	3

1. General Information

1.1 Upgrade Capability

Upgrade from INSITE 8.4.0

1.2 Fault Information System (FIS)

FIS troubleshooting files can be downloaded through Update Manager when available

2. New Base Features

NOTE: No new Advanced ECM Data have been implemented.

3. New Diagnostic Tests

3.1 Aftertreatment Diesel Filter Regeneration Analyzer

This test performs an aftertreatment diesel particulate filter regeneration while monitoring and analyzing data to determine the health of the engine, air handling system, Diesel Oxidation Catalyst, and Diesel Particulate Filter.

4. New Advanced ECM Data

NOTE: No new Advanced ECM Data have been implemented.

5. New Features and Parameters

NOTE: No new Features and Parameters have been implemented.

6. New Product Support

Centry CM2940

7. Supported Languages

English

Translations:

Chinese (Simplified)	Greek	Portuguese
Czech	Indonesian	Romanian
Danish	Italian	Russian
Dutch	Japanese	Spanish

Finnish
French
German

Korean
Norwegian
Polish

Swedish
Turkish

8. Supported Operating Systems

Windows® 7 32-bit and 64-bit
Windows® 8 32-bit and 64-bit
Windows® 8.1 32-bit and 64-bit
Windows® 10 32-bit and 64-bit

NOTE: INSITE 8.4.1 is not supported on the following Operating Systems:

Windows® XP
Windows® Vista
Windows® 7 Starter Edition or Basic Edition
Windows® 8 RT Edition
Windows® 8.1 RT Edition

9. PC Requirements

9.1 Recommended

COMPONENT	REQUIREMENTS (Suggested for new hardware purchases)
Operating System:	Windows 7, 8 or 10 (32-bit or 64-bit)
Processor:	2.1 GHz or greater (Intel i5 or AMD K10)
RAM Memory:	12 GB or greater
Hard Drive:	2 GB or greater available disk space
Media Device:	Dual Layer - Double Density DVD-ROM
Display:	1366 x 768 or greater resolution
Keyboard:	101 Key Enhanced
Pointing Device:	Windows® Compatible Device
Multimedia:	Virtual College training will require multimedia and sound capability
Other Software:	Adobe Acrobat Reader v9.0 and later
Printer:	Windows® Compatible Device
Internet Connection:	Broadband High-Speed (such as DSL or Cable)
Available Ports:	Two USB 2.0 Ports

9.2 Minimum

COMPONENT	REQUIREMENTS (Suggested for use with existing hardware)
Operating System:	Windows 7, 8 or 10 (32-bit or 64-bit)
Processor:	2 GHz or greater (Intel i3 or AMD K10)
RAM Memory:	8 GB

Hard Drive:	2 GB available disk space
Media Device:	DVD-ROM
Display:	Minimum Resolution 1024 x 768
Keyboard:	101 Key Enhanced
Pointing Device:	Windows® Compatible Device
Multimedia:	Any Windows® Compatible Sound Device
Other Software:	Adobe Acrobat Reader v9.0 and later
Printer:	Windows® Compatible Device
Internet	Broadband High-Speed (such as DSL or Cable)
Available Ports:	See datalink adapter manufacturer for port specifications