INSITE™ CENSE

INSTALL UNINSTALL BULLETIN

NOTE: PLEASE DO NOT ATTEMPT TO INSTALL THE SOFTWARE BEFORE READING THIS DOCUMENT.

INSTALLATION STEPS for Installing CENSE


1

1. Type D*:\gdrive\SETUP* in the command line box, then choose **OK** or use choose “Install INSITE CENSE” from the auto play selection menu. (If you use a drive other than D:, substitute the correct drive letter.)

2

Wait while the InstallShield Wizard prepares the installation.

The percent bar displays the Wizard’s progress.




3

Choose **Next** to install CENSE.

Or

Choose **Cancel** to exit Setup and return to Program Manager. (In Windows 95 you return to the desktop.)

Note: *You can choose the Cancel button in any of the Setup windows to exit Setup and abort the installation.*



4

Review the Software License Agreement.. Choose Yes to accept the agreement and install CENSE.


Or

Choose No to exit Setup and return to Program Manager.


Or

Choose Back to return to the previous selection screen.

Note: *You can choose the Back button in any of the Setup windows to return to the previous window.*




5 Review the ReadMe information. Choose Next to continue with the installation of CENSE.



6*a* If you are installing the CENSE software for the first time, it is installed by default in the C:\INTELECT\CENSE directory.


You can specify a different directory by selecting the Browse button and choosing the new directory.

When the path is correct, choose **Next**.



6*b* If you are *reinstalling* CENSE, you see this Warning. Select whether to Continue to install into the same directory or Change to a new directory.


Note: *If you install into the same directory as your current copy of CENSE,* ***all*** *previous program files are destroyed* and you should select Yes to replace all files.



7 Determine whether to install the CENSE program files, CENSE Security, and Engine Series Support.

Select the checkboxes for the components you want to install.

After making your selection(s), choose **Next**.




INSTALLATION STEPS for Installing CENSE (continued)

8 Select the connection type to use to connect your PC to an ECM.

Click the arrow in the Drop Down list box to view the available connection type, then select one by clicking it. (Direct Serial is most often used)


After selecting a connection type, choose **Next**.




9 Select the COM port to use to connect your PC to an ECM.

Click the arrow in the Drop Down list box to view the available COM ports, then select one by clicking it.

After selecting a COM port, choose **Next**.





10 Review the installation selections. If these are acceptable, choose Next.



11 CENSE Setup begins.


The percent bars display progress as files are installed on your hard disk.





12 Installation of the CENSE software is finished. Click **Finish**.


The CENSE program group/folder and icons are added to your Windows desktop. View the ReadMe file by double-clicking its icon before using CENSE.



Uninstalling INSITE for CENSE


1 Open the Uninstall INSITE CENSE icon in the INSITE CENSE folder/group.

You are asked to confirm that you want to delete the application. Click **Yes** to continue, **No** to cancel the uninstall.



2 Choose whether to remove the CENSE calibration database(s). Removing the databases recovers disk space.


Note: Uninstall does not remove existing job data.



3 This window displays the progress of the uninstall, and is typical of most Windows uninstall routines.

You may be asked to confirm deletion of certain files that may be used by other applications. If you are in doubt whether it is safe to delete a file, *do not* delete it.

When the **OK** button is active at the completion of the file removal; click it to finish the uninstall.



4 The Warning pop-up lists any INSITE CENSE components that were not removed automatically. Make a note of the components so that you can remove them manually, if desired, using Explorer or File Manager.

Uninstall is complete. Click **OK** to return to Windows.

